

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M16X180

Article number	01400.160.180
Brand	-
UBB	950351938465
UNSPSC	31161620
EAN	8715492408792
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	180 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

NEN	1555
DIN	931
ISO	4014
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57

Technical Drawing

b (min.): $L \leq 125\text{mm}$	38
d-D	M16
k	10
L (mm)	180
P	2
s	24

