

## Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M16X200

Article number	01400.160.200
Brand	-
UBB	950351938531
UNSPSC	31161620
EAN	8715492408808
PKG. of 25	Full Box Only

### Technical Parameters

Diameter	M16
Length	200 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info  
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

### Standards

ISO	4014
ASME	B18.2.3.1M
DIN	931
NF	E25-112
NEN	1555

### Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57

### Technical Drawing

b (min.): $L \leq 125\text{mm}$	38
d-D	M16
k	10
L (mm)	200
P	2
s	24

