

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M16X260

Article number	01400.160.260
Brand	-
UBB	954351241029
UNSPSC	31161620
EAN	8715492408839
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	260 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

DIN	931
ISO	4014
NF	E25-112
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57

Technical Drawing

b (min.): $L \leq 125\text{mm}$	38
d-D	M16
k	10
L (mm)	260
P	2
s	24

