

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M20X120



Article number	01400.200.120
----------------	---------------

Brand	-
-------	---

UBB	950351194945
-----	--------------

UNSPSC	31161620
--------	----------

EAN	8715492409041
-----	---------------

PKG. of 25	Full Box Only
------------	---------------

Technical Parameters

Diameter (d-D)	M20
Length (L) (mm)	120
Class	8.8
Driving features	Hexagon
Extra info	ISO metric
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.

Standards

ISO	4014
NF	E25-112
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.):	52
125mm<L≤200mm	

Technical Drawing

b (min.): $L > 200\text{mm}$ 65

b (min.): $L \leq 125\text{mm}$ 46

k 12.5

P 2.50

s 30

