

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M20X220

Article number	01400.200.220
Brand	-
UBB	950351939034
UNSPSC	31161620
EAN	8715492409119
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	220 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

NEN	1555
ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65

Technical Drawing

b (min.): $L \leq 125\text{mm}$	46
d-D	M20
k	12.5
L (mm)	220
P	2.5
s	30

