

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M20X240

Article number	01400.200.240
Brand	-
UBB	950351939117
UNSPSC	31161620
EAN	8715492409126
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	240 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

NF	E25-112
ASME	B18.2.3.1M
ISO	4014
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65

Technical Drawing

b (min.): $L \leq 125\text{mm}$	46
d-D	M20
k	12.5
L (mm)	240
P	2.5
s	30

