

## Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M22X70/S=34



Article No.	01400.220.071
Brand	-
UBB	952351082898
UNSPSC	31161620
EAN	8715492409188
PKG. of 25	Full Box Only

### Technical Parameters

Diameter (d-D)	M22
Length (L) (mm)	70
Class	8.8
Driving features	Hexagon
Extra info	ISO metric DIN 931
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Wrench width	34

**Info**  
 ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.

### Standards

ASME	B18.2.3.1M
NEN	1555
DIN	931
ISO	4014
NF	E25-112

**Technical Specification**

**Technical Drawing**

b (min.): 56  
125mm <math>L \le 200\text{mm}</math>

**FABON** OF COURSE  
SETTING THE STANDARD

b (min.):  $L \le 125\text{mm}$  50

b (min.):  $L > 200\text{mm}$  69

P 2.50

k 14

