

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M27X150

Article number	01400.270.150
Brand	-
UBB	950351197914
UNSPSC	31161620
EAN	8715492409645
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M27
Length	150 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

ISO	4014
NF	E25-112
ASME	B18.2.3.1M
DIN	931
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79

Technical Drawing

b (min.): $L \leq 125\text{mm}$	60
d-D	M27
k	17
L (mm)	150
P	3
s	41

