

## Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M30X90

|                |               |
|----------------|---------------|
| Article number | 01400.300.090 |
| Brand          | -             |
| UBB            | 950351198177  |
| UNSPSC         | 31161620      |
| EAN            | 8715492409669 |
| PKG. of 10     | Full Box Only |

### Technical Parameters

|                   |                    |
|-------------------|--------------------|
| Diameter          | M30                |
| Length            | 90 mm              |
| Class             | 8.8                |
| Driving features  | Hexagon            |
| Head shape        | Hexagon head       |
| Material          | Steel              |
| Thread direction  | Right              |
| Surface treatment | Hot dip galvanized |
| Thread            | Metric thread      |

Info  
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

### Standards

|      |            |
|------|------------|
| NF   | E25-112    |
| DIN  | 931        |
| ISO  | 4014       |
| NEN  | 1555       |
| ASME | B18.2.3.1M |

### Technical Specification

|                           |    |
|---------------------------|----|
| b (min.):<br>125mmL≤200mm | 72 |
| b (min.): L200mm          | 85 |

### Technical Drawing

|                                 |      |
|---------------------------------|------|
| b (min.): $L \leq 125\text{mm}$ | 66   |
| d-D                             | M30  |
| k                               | 18.7 |
| L (mm)                          | 90   |
| P                               | 3.5  |
| s                               | 46   |

