

## Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M36X240

Article number	01400.360.240
Brand	-
UBB	954351242191
UNSPSC	31161620
EAN	8715492409911
PKG. of 2	Full Box Only

### Technical Parameters

Diameter	M36
Length	240 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info  
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

### Standards

DIN	931
ISO	4014
NF	E25-112
ASME	B18.2.3.1M
NEN	1555

### Technical Specification

b (min.): 125mmL≤200mm	84
b (min.): L200mm	97

### Technical Drawing

b (min.): $L \leq 125\text{mm}$	78
d-D	M36
k	22.5
L (mm)	240
P	4
s	55

