



Structural assembly set ISO metric thread EN 15048 Steel Hot dip galvanized 8.8/8 M10X50

Article number	01405.100.050
Brand	-
UBB	500574457239
UNSPSC	31161620
EAN	8715494311335
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	50 mm
Class	8.8/8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

Full boxes only. European constructions must comply with the Construction Products Regulation (CPR) in order to ensure the safety of persons and objects. Generally, construction products according to harmonized European standards (hEN standards) should be used for this purpose. Bolting assemblies for non-preloaded structural

Standards

ISO	4014/4032
EN	15048

bolting according to EN 15048-1 are compliant with the CPR. Compared to 'common' bolts ISO 4014/4017 (previously DIN 931/933) and nuts ISO 4032 (DIN 934), bolts and nuts according to EN 15048 are additionally marked with 'SB' (Structural Bolting), and the packaging is provided with the CE-mark. The manufacturer of the assemblies is CE certified for their production. Bolts and nuts are packaged together in single sealed boxes. A Declaration of Performance (DoP) is available. ISO metric

Technical Specification

b (min.): 125mm $L \leq 200$ mm	32
b (min.): $L > 200$ mm	45
b (min.): $L \leq 125$ mm	26
d-D	M10
k	6.4
L (mm)	50
m (max.)	8.4
P	1.5
s	16

Technical Drawing

