



## Structural assembly set ISO metric thread EN 15048 Steel Hot dip galvanized 8.8/8 M10X65

Article number	01405.100.065
Brand	-
UBB	500574457569
UNSPSC	31161620
EAN	8715494311366
PKG. of 100	Full Box Only

### Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	65

### Standards

EN	15048
ISO	4014/4032

#### Info

Full boxes only. European constructions must comply with the Construction Products Regulation (CPR) in order to ensure the safety of persons and objects. Generally, construction products according to harmonized European standards (hEN standards) should be used for this purpose. Bolting assemblies for non-preloaded structural bolting according to EN 15048-1 are compliant with the CPR. The manufacturer of the assemblies is CE certified for their production. Bolts and nuts are

packaged together in single sealed boxes. A Declaration of Performance (DoP) is available.

Class	8.8/8
Driving features	Hexagon
Extra info	ISO metric
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Wrench width (s) (mm)	16

### Technical Specification

b (min.): 125mm <math>L \leq 200\text{mm}</math>	32
b (min.): $L > 200\text{mm}$	45
b (min.): $L \leq 125\text{mm}$	26
k	6.4
m (max.)	8.4
P	1.50
s	16

### Technical Drawing

