



Structural assembly set ISO metric EN 15048 Steel Hot dip galvanized 8.8/8 M12X90

Article No.	01405.120.090
Brand	-
UBB	500574459052
UNSPSC	31161620
EAN	8715494283786
PKG. of 50	Full Box Only

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	90

Standards

ISO	4014/4032
EN	15048

Info	<p>Full boxes only. European constructions must comply with the Construction Products Regulation (CPR) in order to ensure the safety of persons and objects. Generally, construction products according to harmonized European standards (hEN standards) should be used for this purpose. Bolting assemblies for non-preloaded structural bolting according to EN 15048-1 are compliant with the CPR. The manufacturer of the assemblies is CE certified for their production. Bolts and nuts are packaged together in single sealed boxes.</p>
------	---

A Declaration of Performance (DoP) is available.

SETTING THE STANDARD
IN JOINING SOLUTIONS

Class 8.8/8

Driving features Hexagon

Extra info ISO metric

Head shape Hexagon head

Material Steel

Thread direction Right

Surface treatment Hot dip galvanized

Thread Metric thread

Wrench width (s)
(mm) 18

Technical Specification

b (min.): 36
125mm $L \leq 200\text{mm}$

b (min.): $L > 200\text{mm}$ 49

b (min.): $L \leq 125\text{mm}$ 30

k 7.5

m (max.) 10.8

P 1.75

s 18

Technical Drawing

