

Hexagon head screw ISO metric thread DIN 933 Steel Hot dip galvanized 8.8 M8X10

Article number	01410.080.010
Brand	-
UBB	500645014191
UNSPSC	31161620
EAN	8717077051058
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	10 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

ASME	B18.2.3.1M
NF	E25-114
ISO	4017
DIN	933
NEN	1568

Technical Specification

d-D	M8
k	5.3
L (mm)	10

Technical Drawing

P	1.25
s	13

