

Hexagon head screw ISO metric thread DIN 933 Steel Hot dip galvanized 8.8 M30X170

Article number	01410.300.170
Brand	-
UBB	500644664723
UNSPSC	31161620
EAN	8717077015364
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M30
Length	170 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

ISO	4017
DIN	933
NF	E25-114
NEN	1568
ASME	B18.2.3.1M

Technical Specification

d-D	M30
k	18.7
L (mm)	170

Technical Drawing

P	3.5
s	46

