

## Hexagon head screw ISO metric thread DIN 933 Steel Hot dip galvanized 8.8 M30X180

Article number	01410.300.180
Brand	-
UBB	500644664806
UNSPSC	31161620
EAN	8717077015371
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	M30
Length	180 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info  
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

### Standards

DIN	933
ASME	B18.2.3.1M
NF	E25-114
ISO	4017
NEN	1568

### Technical Specification

d-D	M30
k	18.7
L (mm)	180

### Technical Drawing

P	3.5
s	46

