

Hexagon head screw ISO metric thread DIN 933 Steel Hot dip galvanized 8.8 M30X190

Article number	01410.300.190
Brand	-
UBB	500644664988
UNSPSC	31161620
EAN	8717077015388
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M30
Length	190 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

ISO	4017
ASME	B18.2.3.1M
DIN	933
NF	E25-114
NEN	1568

Technical Specification

d-D	M30
k	18.7
L (mm)	190

Technical Drawing

P	3.5
s	46

