

Hexagon head bolt oversized thread DIN 931 Steel Hot dip galvanized 8.8 M20X65

Article number	01420.200.065
Brand	-
UBB	950351206905
UNSPSC	31161620
EAN	8715492411525
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	65 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). oversized

Standards

ISO	4014
ASME	B18.2.3.1M
DIN	931
NEN	1555
NF	E25-112

b (min.): 125mm $L \leq 200$ mm	52
b (min.): $L > 200$ mm	65
b (min.): $L \leq 125$ mm	46
d-D	M20
k	12.5
L (mm)	65
P	2.5
s	30

