

Hexagon head screw oversized thread DIN 933 Steel Hot dip galvanized 8.8 M12X45

Article number	01430.120.045
Brand	-
UBB	500621742765
UNSPSC	31161620
EAN	8715494504881
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	45 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). oversized

Standards

NF	E25-114
DIN	933
ASME	B18.2.3.1M
ISO	4017
NEN	1568

Technical Specification

d-D	M12
k	7.5
L (mm)	45
P	1.75
s	19

Technical Drawing

