

Hexagon head screw oversized thread DIN 933 Steel Hot dip galvanized 8.8 M12X55

Article number	01430.120.055
Brand	-
UBB	500621742849
UNSPSC	31161620
EAN	8715494504898
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	55 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). oversized

Standards

NEN	1568
NF	E25-114
ASME	B18.2.3.1M
DIN	933
ISO	4017

Technical Specification

d-D	M12
k	7.5
L (mm)	55
P	1.75
s	19

Technical Drawing

