

Hexagon head screw oversized thread DIN 933 Steel Hot dip galvanized 8.8 M14X60

| | |
|----------------|---------------|
| Article number | 01430.140.060 |
| Brand | - |
| UBB | 954351343171 |
| UNSPSC | 31161620 |
| EAN | 8715492412416 |
| PKG. of 50 | Full Box Only |

Technical Parameters

| | |
|-------------------|--------------------|
| Diameter | M14 |
| Length | 60 mm |
| Class | 8.8 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Hot dip galvanized |
| Thread | Metric thread |

Info

Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). oversized

Standards

| | |
|------|------------|
| ASME | B18.2.3.1M |
| DIN | 933 |
| ISO | 4017 |
| NEN | 1568 |
| NF | E25-114 |

Technical Specification

| | |
|--------|-----|
| d-D | M14 |
| k | 8.8 |
| L (mm) | 60 |
| P | 2 |
| s | 22 |

Technical Drawing

