



Hexagon head screw oversized thread DIN 933 Steel Hot dip galvanized 8.8 M16X100

Article number	01430.160.100
Brand	-
UBB	500621744175
UNSPSC	31161620
EAN	8715494506687
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M16
Length (L) (mm)	100
Class	8.8
Driving features	Hexagon
Extra info	oversized
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Standards

ISO	4017
ASME	B18.2.3.1M
NF	E25-114
DIN	933

Info
 Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized).

Technical Specification

FARORY
INDUSTRIAL SOLUTIONS

k	10
P	2
s	24

Technical Drawing

