

## Hexagon head screw oversized thread DIN 933 Steel Hot dip galvanized 8.8 M27X80

Article number	01430.270.080
Brand	-
UBB	500621746311
UNSPSC	31161620
EAN	8715494506908
PKG. of 10	Full Box Only

### Technical Parameters

Diameter	M27
Length	80 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

#### Info

Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). oversized

### Standards

ISO	4017
DIN	933
NF	E25-114
NEN	1568
ASME	B18.2.3.1M

Technical Specification

d-D	M27
k	17
L (mm)	80
P	3
s	41

Technical Drawing

