



Hexagon head screw oversized thread DIN 933 Steel Hot dip galvanized 8.8 M30X60

Article number 01430.300.060

Brand -

UBB 500621746493

UNSPSC 31161620

EAN 8715494506915

PKG. of 10 Full Box Only

Technical Parameters

Diameter (d-D)	M30
Length (L) (mm)	60
Class	8.8
Driving features	Hexagon
Extra info	oversized
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Standards

NF	E25-114
ISO	4017
DIN	933
ASME	B18.2.3.1M

Info
Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized).

Technical Specification

k	18.7
P	3.50
s	46

Technical Drawing

