



Hexagon head screw oversized thread DIN 933 Steel Hot dip galvanized 8.8 M36X90

Article number 01430.360.090

Brand -

UBB 500621747145

UNSPSC 31161620

EAN 8715494506984

PKG. of 5 Full Box Only

Technical Parameters

Diameter (d-D)	M36
Length (L) (mm)	90
Class	8.8
Driving features	Hexagon
Extra info	oversized
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Standards

ISO	4017
ASME	B18.2.3.1M
DIN	933
NF	E25-114

Info
Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized).

Technical Specification

k	22.5
P	4
s	55

Technical Drawing

