

Hexagon nut DIN 934 Steel  
Hot dip galvanized |8| M30

|                |               |
|----------------|---------------|
| Article number | 01500.300.001 |
| Brand          | -             |
| UBB            | 950355023769  |
| UNSPSC         | 31161727      |
| EAN            | 8715492413161 |
| PKG. of 10     | Full Box Only |

Technical Parameters

|                   |                    |
|-------------------|--------------------|
| Diameter          | M30                |
| Class             | 8                  |
| Driving features  | Hexagon            |
| Material          | Steel              |
| Thread direction  | Right              |
| Surface treatment | Hot dip galvanized |
| Thread            | Metric thread      |

Info

ISO metric hot dip galvanized nuts are manufactured with thread tolerance class 6H and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6az before coating.As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced disadvantageously as the thread will be protected by the zinc

Standards

|     |         |
|-----|---------|
| NF  | E25-401 |
| DIN | 934     |
| NEN | 1560    |

## Technical Specification

|     |     |
|-----|-----|
| d-D | M30 |
| m   | 24  |
| P   | 3.5 |
| s   | 46  |

## Technical Drawing

