

Hexagon nut DIN 934 Steel
Hot dip galvanized |8| M42

Article number	01500.420.001
Brand	-
UBB	950355306909
UNSPSC	31161727
EAN	8715492413208
PKG. of 3	Full Box Only

Technical Parameters

Diameter	M42
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

ISO metric hot dip galvanized nuts are manufactured with thread tolerance class 6H and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6az before coating.As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced disadvantageously as the thread will be protected by the zinc

Standards

DIN	934
NEN	1560
NF	E25-401

Technical Specification

d-D	M42
m	34
P	4.5
s	65

Technical Drawing

