

Hexagon nut ISO-Metric
thread ISO 4032 Steel Hot
dip galvanized 8 M12

Article number	01510.120.001
Brand	-
UBB	500613233955
UNSPSC	31161727
EAN	8715494433242
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

ISO metric hot dip galvanized nuts are manufactured with thread tolerance class 6H and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6az before coating.As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced disadvantageously as the thread will be protected by the zinc

Standards

ISO	4032
-----	------

Technical Specification

d-D	M12
m (max.)	10.8
P	1.75
s	18

Technical Drawing

