



Hexagon nut ISO-Metric thread ISO 4032 Steel Hot dip galvanized 8 M33

Article number	01510.330.001
Brand	-
UBB	500613234862
UNSPSC	31161727
EAN	8715494433334
PKG. of 5	Full Box Only

Technical Parameters

Diameter (d-D)	M33
Class	8
Driving features	Hexagon
Extra info	ISO metric
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Standards

ISO	4032
-----	------

Info

ISO metric hot dip galvanized nuts are manufactured with thread tolerance class 6H and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6az before coating. As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced

disadvantageously
as the thread will be
protected by the zinc
layer of the mating
part.

Technical Specification

m (max.)	28.7
P	3.50
s	50

Technical Drawing

