



**Hexagon thin nut oversized thread DIN 439 2 Steel Hot dip galvanized 04 M30**

Article number	01580.300.001
Brand	-
UBB	500621747558
UNSPSC	31161727
EAN	8715494507028
PKG. of 25	Full Box Only

**Technical Parameters**

Diameter	M30
Class	04
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

Oversized hot dip galvanized nuts are manufactured with thread tolerance class 6AZ and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6g before coating. As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced disadvantageously

**Standards**

NEN	2334-B
ASME	B18.2.4.5M
NF	E25-405-1
ISO	4035
DIN	439-2

as the thread will be  
protected by the zinc  
layer of the mating  
part.oversized

## Technical Specification

d-D	M30
m	15
P	3.5
s	46

## Technical Drawing

