



Hexagon thin nut ISO-Metric thread DIN 439 2 Steel Hot dip galvanized 04 M14

Article number	01586.140.001
Brand	-
UBB	951355062518
UNSPSC	31161727
EAN	8715492413574
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M14
Class	04
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

ISO metric hot dip galvanized nuts are manufactured with thread tolerance class 6H and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6az before coating.As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced disadvantageously

Standards

ASME	B18.2.4.5M
ISO	4035
DIN	439-2
NEN	2334-B
NF	E25-405-1

as the thread will be
protected by the zinc
layer of the mating
part.ISO metric

Technical Specification

d-D	M14
m	7
P	2
s	22

Technical Drawing

