



**PEINER HV structural bolt
EN 14399-4 Steel Plain 10.9
M16X65**

Article number	04005.160.065
Brand	-
UBB	500504245688
UNSPSC	31161614
EAN	8715494440967
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	65 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement. PEINER
HV-bolts and
corresponding
HV-nuts and HV-
washers, sizes
M12 up to M36
are specified in EN
14399-4 and EN
14399-6. Diameters
M39 up to M72
are defined in
DAST directive
021. PEINER HV-
bolts with associated
HV-nuts and HV-
washers may be

Standards

EN	14399-4
----	---------

FABORY used only as a set
from one and the
same supplier.

Technical Specification

b	28
d-D	M16
k	10
L (mm)	65
P	2
s	27

Technical Drawing

