

Hexagon head bolt DIN 931 Steel Plain 10.9 M6X55

Article number	04100.060.055
Brand	-
UBB	953351005822
UNSPSC	31161620
EAN	8715492114136
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	55 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-112
DIN	931
ISO	4014
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
k	4
L (mm)	55
P	1
s	10

Technical Drawing

