

Hexagon head bolt ISO 4014 Steel Zinc plated 10.9 M10X120

Article number	04101.100.120
Brand	-
UBB	500648297942
UNSPSC	31161620
EAN	8717077206748
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	120 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

DIN	931
ISO	4014
NF	E25-112
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	120
P	1.5
s	16

Technical Drawing

