

Hexagon head bolt ISO 4014 Steel Zinc plated 10.9 M12X80

Article number	04101.120.080
Brand	-
UBB	500648299278
UNSPSC	31161620
EAN	8717077206878
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	80 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ASME	B18.2.3.1M
DIN	931
ISO	4014
NEN	1555
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	80
P	1.75
s	18

Technical Drawing

