

Hexagon head bolt DIN 931 Steel Zinc plated 10.9 M16X75

Article number	04102.160.075
Brand	-
UBB	500648132933
UNSPSC	31161620
EAN	8717077209169
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	75 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-112
DIN	931
NEN	1555
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	75
P	2
s	24

Technical Drawing

