

Hexagon head bolt DIN 931 Steel Zinc plated 10.9 M24X180

Article number	04102.240.180
Brand	-
UBB	500648139961
UNSPSC	31161620
EAN	8717077209862
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	180 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ASME	B18.2.3.1M
ISO	4014
NF	E25-112
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	180
P	3
s	36

Technical Drawing

