

## Hexagon head bolt DIN 931 Steel Zinc plated yellow passivated 10.9 M14X100/ S=22



Article No.	04104.140.100
Brand	-
UBB	500614316445
UNSPSC	31161620
EAN	8715494454513
PKG. of 1	Full Box Only

### Technical Parameters

Diameter (d-D)	M14
Length (L) (mm)	100
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread
Wrench width	22
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

### Standards

NF	E25-112
ASME	B18.2.3.1M
DIN	931
ISO	4014
NEN	1555

### Technical Specification

b (min.): 125mm<L≤200mm	40
k	8.8
s	22
b (min.): L≤125mm	34
b (min.): L>200mm	53

### Technical Drawing



