

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 10.9 M16X110



Article No.	04104.160.110
Brand	-
UBB	500614316775
UNSPSC	31161620
EAN	8715494454544
PKG. of 1	Full Box Only

Technical Parameters

Diameter (d-D)	M16
Length (L) (mm)	110
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	931
NF	E25-112
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mm<L≤200mm	44
b (min.): L>200mm	57
b (min.): L≤125mm	38
k	10
P	2
s	24

Technical Drawing

