

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M8X60



Article No.	04105.080.060
Brand	-
UBB	500505560473
UNSPSC	31161620
EAN	8715494439039
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M8
Length (L) (mm)	60
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr(VI) free - flZn/nc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
DIN	931
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mm<L≤200mm	28
b (min.): L≤125mm	22
k	5.3
P	1.25
s	13

Technical Drawing

