

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M8X80

Article number	04105.080.080
Brand	-
UBB	500645020602
UNSPSC	31161620
EAN	8717077051706
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	80 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ISO	4014
DIN	931
ASME	B18.2.3.1M
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	80
P	1.25
s	13

Technical Drawing

