

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M10X90



Article number 04105.100.090

Brand -

UBB 500505561208

UNSPSC 31161620

EAN 8715494439176

PKG. of 100 Full Box Only

Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	90
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr(VI) free - flZn/nc
Thread	Metric thread
Wrench width (s) (mm)	17
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

NF	E25-112
DIN	931
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm<L≤200mm	32
b (min.): L>200mm	45
b (min.): L≤125mm	26
k	6.4
P	1.50

Technical Drawing



