

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M10X90



| | |
|-------------|---------------|
| Article No. | 04105.100.090 |
| Brand | - |
| UBB | 500505561208 |
| UNSPSC | 31161620 |
| EAN | 8715494439176 |
| PKG. of 100 | Full Box Only |

Technical Parameters

| | |
|--------------------------|---|
| Diameter (d-D) | M10 |
| Length (L) (mm) | 90 |
| Class | 10.9 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc flake Cr(VI) free - flZn/nc |
| Thread | Metric thread |
| Wrench width (s) (mm) | 17 |
| Info | A zinc flake coating eliminates the risk of hydrogen embrittlement. |

Standards

| | |
|------|------------|
| ASME | B18.2.3.1M |
| NF | E25-112 |
| ISO | 4014 |
| DIN | 931 |

Technical Specification

| | |
|---|------|
| b (min.): 125mm $L \leq 200\text{mm}$ | 32 |
| b (min.): $L > 200\text{mm}$ | 45 |
| b (min.): $L \leq 125\text{mm}$ | 26 |
| k | 6.4 |
| P | 1.50 |

Technical Drawing



