

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M12X50



Article number 04105.120.050

Brand -

UBB 500505561612

UNSPSC 31161620

EAN 8715494439268

PKG. of 100 Full Box Only

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	50
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr(VI) free - flZn/nc
Thread	Metric thread
Wrench width (s) (mm)	19
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	931
NF	E25-112
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	36
b (min.): $L > 200\text{mm}$	49
b (min.): $L \leq 125\text{mm}$	30
k	7.5
P	1.75

Technical Drawing



