

## Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M14X80



Article No.	04105.140.080
Brand	-
UBB	500505562529
UNSPSC	31161620
EAN	8715494439411
PKG. of 50	Full Box Only

### Technical Parameters

Diameter (d-D)	M14
Length (L) (mm)	80
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr(VI) free - flZn/nc
Thread	Metric thread
Wrench width (s) (mm)	22
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

### Standards

DIN	931
NF	E25-112
ISO	4014
ASME	B18.2.3.1M

### Technical Specification

b (min.): 125mm <math>L \leq 200\text{mm}</math>	40
b (min.): $L > 200\text{mm}$	53
b (min.): $L \leq 125\text{mm}$	34
k	8.8
P	2

### Technical Drawing



