

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M14X90

Article number	04105.140.090
Brand	-
UBB	500505562602
UNSPSC	31161620
EAN	8715494439435
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	90 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ISO	4014
NF	E25-112
NEN	1555
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	90
P	2

Technical Drawing



