

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M14X100

Article number	04105.140.100
Brand	-
UBB	500505562784
UNSPSC	31161620
EAN	8715494439442
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	100 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

NEN	1555
NF	E25-112
ASME	B18.2.3.1M
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	100
P	2

Technical Drawing



