

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M16X80



| | |
|-------------|---------------|
| Article No. | 04105.160.080 |
| Brand | - |
| UBB | 500505563105 |
| UNSPSC | 31161620 |
| EAN | 8715494439510 |
| PKG. of 25 | Full Box Only |

Technical Parameters

| | |
|-------------------|---|
| Diameter (d-D) | M16 |
| Length (L) (mm) | 80 |
| Class | 10.9 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc flake Cr(VI) free - flZn/nc |
| Thread | Metric thread |
| Info | A zinc flake coating eliminates the risk of hydrogen embrittlement. |

Standards

| | |
|------|------------|
| DIN | 931 |
| ASME | B18.2.3.1M |
| NF | E25-112 |
| ISO | 4014 |

Technical Specification

| | |
|----------------------------|----|
| b (min.): 125mm<L≤200mm | 44 |
| b (min.): L>200mm | 57 |
| b (min.): L≤125mm | 38 |
| k | 10 |
| P | 2 |
| s | 24 |

Technical Drawing

