

## Hexagon head bolt DIN 931 Steel Plain 12.9 M6X30



|                |               |
|----------------|---------------|
| Article number | 04108.060.030 |
| Brand          | -             |
| UBB            | 955351407353  |
| UNSPSC         | 31161620      |
| EAN            | 8715493849532 |
| PKG. of 200    | Full Box Only |

### Technical Parameters

|                   |   |
|-------------------|---|
| Diameter (d-D)    | M6  |
| Length (L) (mm)   | 30  |
| Class             | 12.9  |
| Driving features  | Hexagon   |
| Head shape        | Hexagon head  |
| Material          | Steel   |
| Thread direction  | Right   |
| Surface treatment | Plain   |
| Thread            | Metric thread   |
| Info              | Warning:<br>electroplating of<br>these products may<br>cause hydrogen<br>embrittlement. |

### Standards

|      |            |
|------|------------|
| ISO  | 4014       |
| ASME | B18.2.3.1M |
| NF   | E25-112    |
| DIN  | 931        |

### Technical Specification

|                            |    |
|----------------------------|----|
| b (min.):<br>125mm<L≤200mm | 24 |
| b (min.): L≤125mm          | 18 |
| k                          | 4  |
| P                          | 1  |
| s                          | 10 |

### Technical Drawing

