

## Hexagon head bolt DIN 931 Steel Plain 12.9 M8X50



Article number	04108.080.050
Brand	-
UBB	955351407841
UNSPSC	31161620
EAN	8715493849587
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M8
Length (L) (mm)	50
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

### Standards

NF	E25-112
DIN	931
ASME	B18.2.3.1M
ISO	4014

### Technical Specification

b (min.): 125mm<L≤200mm	28
b (min.): L≤125mm	22
k	5.3
P	1.25
s	13

### Technical Drawing

